

Product Specification



Golledge Electronics Ltd
Ashwell Park
ILMINSTER
Somerset
TA19 9DX
England

Tel: +44 1460 256 100
Fax: +44 1460 256 101

Golledge

Email: sales@golledge.com
Web: www.golledge.com

Quartz Crystal

Part Number: **MA01377**

Associated Drawing Number: **D0119-A**

Electrical Specifications

<i>Frequency:</i>	28.63636MHz
<i>Product:</i>	HC49/351JF
<i>Cut:</i>	AT
<i>Mode:</i>	Fundamental
<i>Calibration tolerance at 25°C:</i>	±30ppm
<i>Temperature stability:</i>	±50ppm
<i>Operating temperature range:</i>	-10 to +60°C
<i>Circuit condition:</i>	30pF
<i>Equivalent series resistance:</i>	30Ω max
<i>Static capacitance:</i>	7pF max
<i>Ageing:</i>	±3ppm max first year
<i>Test drive level:</i>	100μW

Issue No:	01					
Date:	17 Feb 05					
Change Request No:	01053					
Raised By:	JPG					