


Ch. A Data

Sampling CLK = 65MHz


Two's Complement

2.00Vp-p




Input Signal wave form (Vin+ A)



- $f_{in} = 6.4\text{MHz}$
- $\Delta V_{in+ A} = 312\text{mV}$
- $V_{cm} = 0.8\text{V}$




Observation point of Vin+AI-A



Ch. A Data



Ch. A Data FFT



ADCBased0

